

Xerox® DocuMate™ 3220

Versatility and quality

- Advanced colour scanner at 23 ppm / 46 ipm*
- Robust full version software bundle
- Flexible. Flatbed or DADF scanning perfect for a wide variety of documents
- OneTouch scanning to PDF, just one touch to your destination
- PDF and Searchable PDF file creation
- Easy operation front panel buttons

* 200dpi B&W



All-round Performance Scanner

No longer is information held captive on paper. The Xerox® DocuMate™ 3220 is a next generation duplex scanner that combines an A4/US Letter sized flatbed and 50-sheet* capacity Duplex Automatic Document Feeder (DADF) to create an entry level scanner with all the best features of higher-end products. It can easily support the scanning needs of individuals in small and home offices or workgroups in the corporate world.

Perfect for a wide variety of documents

The Xerox® DocuMate™ 3220 includes a powerful and robust productivity software bundle that provides all the tools for a document centric professional who needs to better organise, manipulate and communicate paper in their business. Scan checks, documents, business cards, credit cards, photos or thick card stock with one touch simplicity.


The elegant front panel provides simple single button control for at-device scanning to any of 9 presets and up to 99 customisable OneTouch scan profiles (email, folder, printer, or any other application or device). Easy-to-use Visioneer OneTouch makes scanning with one button simple. Press a button on the front panel and your document is scanned.

Optimised for Front-Office

Any business or individual that needs to have better control of its paper volume will benefit from this scanner. Real estate, insurance, education, financial services, retail and healthcare offices will be impressed with this scanner's capabilities to securely process a variety of documents including plastic cards, photos, receipts and handwritten notes and more.

The DocuMate™ 3220 can be used for personal finances, organisation, document archiving, backup, sharing documents by email or network, collaborating with a group, reusing text from a printed document into your own electronic document without retyping, etc. There is almost no limit to the ways you can be more productive and organised.

Flatbed – For scanning fragile or thicker documents, business cards and bounded materials.




DADF – To efficiently scan in forms, bills, invoices and pages of documents

Xerox® DocuMate™ 3220 Software Solutions

Visioneer®

OneTouch

OneTouch provides the most efficient ease-of-use scanning experience to improve your work flow. OneTouch enables the Xerox® DocuMate™ 3220 scanner to send your scanned documents to nearly any destination of your choice all at the touch of a button. The files can be automatically delivered to a specific folder, email, Microsoft Office Application, a local or network printer, a custom application or your cloud storage.



Acuity

With the use of advanced algorithms and dynamic thresholding, Acuity aims to improve the visual clarity of every document that you scan. This technology enables your scanner to instantly correct documents containing imperfections, it improves the overall quality

of scanned images, increases increases optical character recognition (OCR) accuracy and most importantly saves your time.

DriverPLUS

DriverPLUS is a new generation of innovative driver technology for Xerox® DocuMate™ scanners that enables a superior experience for both users and system integrators. DriverPLUS is based on the most current TWAIN 2.2 specifications, and combines the features of advanced 32- and 64-bit native Windows-based TWAIN and WIA drivers.

Nuance®

OmniPage® Pro

OmniPage Pro provides a precise OCR and layout retention solution that quickly transforms scanned documents into editable and formatted text. The text can then be used in virtually any word processing, desktop or web publishing program.


PDF Converter

Nuance PDF Converter is the smarter PDF software choice for businesses. It combines superior Microsoft Office Support, powerful functionality, built-in intelligence, DMS integration and intuitive ease of use. Nuance

PDF converter provides everything you need in order to create, convert, edit, assemble and securely share PDF files.

PaperPort®

Millions of professionals rely on PaperPort to save time and money by efficiently converting paper into digital documents. PaperPort works with Xerox® scanners to turn paper documents into digital documents, it also helps you to manage them along with all other electronic documents in one convenient and easy-to-use filing system. PaperPorts large, clear item thumbnails allows you to visually organise, retrieve and use your scanner documents, including Word files, spreadsheets, PDF files and even digital photos.



Xerox® DocuMate™ 3220 Product Specifications	
Type	Desktop DADF with Flatbed
Scan Speed Black & White @ 200 dpi Colour @ 150 dpi	23 ppm simplex / 46 ipm duplex 17 ppm simplex / 34 ipm duplex
Image Sensor	Dual CIS (Contact Image Sensor)
Light Source	Light Emitting Diode (LED)
Optical Resolution	600 dpi
Background	Black
Output Bit Depth	24-bit colour, 8-bit grayscale, 1-bit black & white
Interface	Hi-speed USB 2.0 (USB 1.1 compatible)
Dimensions	17.9"(w) x 13"(d) x 5.5"(h) (453 x 330 x 139 mm)
Weight	10 lbs. (4.6 kg)
Flatbed Maximum Document Size	8.5" x 11.78" (216 x 299 mm)
DADF Minimum Document Size	3.5" x 3.5" (89 x 89 mm)
DADF Maximum Document Size	8.75" x 38" (222 x 965 mm)
Maximum Document Weight (DADF)	28 lb. (105 g/m²)
Card Scanning	Business cards and non-embossed cards on flatbed only
DADF Capacity	50 sheets
Duty Cycle	1,500 pages/day



For more information or detailed product specifications, please call or visit us at
101 Waterloo Road, Macquarie Park, NSW 2113
Australia 1300 172 855
www.fujixerox.com.au

©2015 Xerox Corporation and Fuji Xerox Asia Pacific Pte Ltd. All rights reserved. Xerox®, Fuji Xerox Asia Pacific Pte Ltd, Xerox and Design® and DocuMate™ and DocuShare® are trademarks of Xerox Corporation in the United States and/or other countries. Visioneer and OneTouch® are trademarks of Visioneer, Inc. Nuance®, PaperPort® and OmniPage® are trademarks of Nuance Communications, Inc. or its affiliates in the United States and/or other countries. Microsoft®, SharePoint®, Windows Vista®, Windows®, the Windows logo and XP® are trademarks of Microsoft Corporation in the United States and/or other countries. Intel® and Pentium® are trademarks of Intel Corporation in the U.S. and/or other countries. Universal Serial Bus is a trademark of USB Implementers Forum, Inc. (USB-IF). TWAIN™ is a trademark of TWAIN Working Group. ISIS® is a trademark of EMC Corporation. All other trademarks are the property of their respective owners and are hereby acknowledged. Prices, features, specifications, capabilities, appearance and availability of Xerox products and services are subject to change without notice. MARS5008

Minimum System Requirements

PC

- Intel® Pentium® 4
- Windows® 8 / 7 / Vista® / XP®
- 2GB RAM
- 350MB free hard disk space
- DVD-ROM drive
- USB Port

MAC

- 1.6 GHz or faster PowerPC G5 or 1.83 GHz or faster Intel Core processor
- Mac OS® X v10.4, v10.5, or later
- 2GB RAM
- 350MB free hard disk space
- CD-ROM drive
- USB Port

Software

(PC Software):

- Visioneer OneTouch with Acuity
- Nuance PDF Converter
- Nuance PaperPort
- Nuance OmniPage Pro
- Scanner Drivers: Visioneer DriverPLUS, TWAIN & Microsoft Windows Image Acquisition (WIA)

(Mac Software):

- ExactScan 2 Lite Capture Application
- NewSoft Presto! PageManager