

EX-i C9065 / C9070

Print Server Powered by Fiery®

World class colour output and simplified document layout and composition, all in a more efficient, integrated workflow.

Accurate, Consistent Colour.

Accurately reproduce corporate and other spot colour with Fiery® Spot-On™ to ensure consistency. Use default colour settings for great colour quality out of the box, or use optional tools, like Fiery® Color Profiler Suite, to adjust and refine colour.

Turn Up The Impact With Personalisation.

With Fiery® FreeForm™ Create, you can quickly and simply personalise existing files for free – with no additional VDP software required. Add variable elements such as text, images, or barcodes with just a few clicks.

Streamline Document Layout And Composition.

Simplify job preparation with Fiery® Impose (optional) and save time by automating common imposed jobs, such as business cards, postcards, and brochures. Manage tabs, media selections, apply last minute edits, and assign multiple finishing requirements in an intuitive, visual interface with the standard Fiery® Compose software.

Affordable Integration.

Standard Fiery® JDF connectivity boosts digital workflow efficiency by integrating with existing prepress, web-to-print, or MIS/ERP systems to eliminate manual touchpoints, errors, and resource waste.

EX-i C9065 / C9070 Print Server for the PrimeLink™ C9070 / C9065 Printer



EX-i C9065 / C9070 Print Server Powered by Fiery®

Fiery Driven™ Engines

- PrimeLink C9070 / C9065 Printer
- Supports all engine finishing devices

Platform

- Fiery® FS350 software

Fiery® Software

- Fiery® Command WorkStation®
- Fiery® Drivers for Windows and Mac
 - Section 508 Usability
 - WHQL certification, PackageAware (Windows)
 - Customise drivers for cost control
- Fiery® WebTools™
- Hot Folders/Virtual Printers
- Fiery® Remote Scan

Fiery® Colour And Imaging

- ICC-based Fiery® colour management
- Fiery® Spot-On™
- PANTONE® Colour Enabled
- Image smoothing
- Fiery® ImageViewer curve presets
- Calibration
 - Fiery® Calibrator
 - ColorCal (standard, off the glass)
 - EFI™ ES-2000 spectrophotometer (optional)

Performance

- SmartRIP
- Spool-RIP-print simultaneously
- Scan-RIP-print simultaneously

Document Management

- Standard support for XLS media
- Fiery® Compose
- Fiery® VUE for visual booklet creation
- Bi-directional paper catalog management
- Booklet printing
- Automatic two-sided printing
- Cover selection
- N-up
- Watermarks
- Sample print
- Output tray selection
- Fiery® Direct Mobile Printing
- Fiery® Go (Android™ and iOS)
- Fiery® FreeForm™ Create

Network Connectivity

- JDF/JMF

Security

- Secure erase
- Encryption of critical information
- Access controls
- Port blocking
- IP Filtering
- IPsec network encryption
- Secure connections using HTTPs
- Secure Printing
- Closed architecture prevents installation of unauthorised programs that could potentially expose the system to vulnerabilities

- Digitally signed software updates
- PostScript® security

EMC

- C-TICK (Australia and New Zealand)
- BSMI – Taiwan
- MSIP – Korea

Safety

- CB Scheme
- BSMI – Taiwan

Fiery® Options

- Fiery® Impose
- Fiery® Compose
- Fiery® Color Profiler Suite* with EFI™ ES-2000 spectrophotometer

Workflow Integration

- FreeFlow Digital Workflow Collection
- Fiery® API
- Native Fiery® JDF

*: Free trial in demo mode

Print Server [EX-i C9065 / C9070 Print Server Powered by Fiery®]

Item	Description
Type	Main unit built-in type
CPU	Intel® Core™ i3-6100 Processor (3.7 GHz)
Storage device	Hard disk: 500 GB
Memory capacity	4 GB (Max: 4 GB)
Server Operation System	Linux
Page Description Language	Adobe® PostScript® Level 1, 2, Adobe® PostScript® 3™, Enhanced PCL6 / PCL5
Print Data Format	Adobe® PDF, EPS, TIFF Microsoft Native Formats (doc/x, xls/x, pub/x, ppt/x) via the Fiery® Drivers or Fiery® Hot Folders

Item	Description
Supported Operating System	Windows 10 (32 bit / 64 bit), Windows 8.1 (32 bit / 64 bit) Windows Server 2019 (64 bit), Windows Server 2016 (64 bit) Windows Server 2012 R2 (64 bit), Windows Server 2012 (64 bit) macOS 10.15 Catalina, 10.14 Mojave, 10.13 High Sierra, 10.12 Sierra OS X 10.11 El Capitan
Interface	Ethernet 1000BASE-T / 100BASE-TX / 10BASE-T, USB3.0 x 2, USB2.0 x 4
Network Protocol	TCP/IP, AppleTalk*, Bonjour, SNMP, Port 9100, IPP, FTP, SMB, WSD*, Point and Print, Print via Email (PS/PDF), IPv6, LDAP
Power Supply	AC100-240 V +/- 10 %, 3 A (100 V) / 1.5 A (240 V), 50/60 Hz common
Maximum Power Consumption	0.2 kW

*1: AppleTalk is not supported by Mac OS X 10.6 Snow Leopard or later.

*2: WSD stands for Web Services on Devices.

Adobe, Adobe logo, PostScript, PostScript logo and Adobe PDF are either registered trademarks or trademarks of Adobe in the United States and/or other countries. All product names and company names mentioned in this brochure are trademarks or registered trademarks of their respective companies. The product specifications, appearance and other details in this brochure are subject to change without notice for improvements. The available model varies depending on the country/region. Please ask the sales representatives for details.

FUJIFILM

For more information or detailed product specifications, please call or visit us at

FUJIFILM Business Innovation Australia Pty Ltd

8 Khartoum Road MACQUARIE PARK NSW 2113 Australia
Tel. +61 2 9856 5000

fujifilm.com/fbau

FUJI XEROX 

This catalog includes Fuji Xerox product(s), licensed from Xerox Corporation. The distributor of the product(s) is FUJIFILM Business Innovation Corp. Xerox, Xerox and Design, Fuji Xerox and Design as well as FreeFlow and PrimeLink are registered trademarks or trademarks of Xerox Corporation in Japan and/or other countries.

FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation.

The information is as of April, 2021. PIC-0144 AU (2002-R1)