



**NEW**

# Proof with Pantone Precision

## INTRODUCING THE NEW EPSON SURECOLOR P7070/P9070

- Superior D-max with outstanding image stability
- Ultimate gamut with up to 99% Pantone coverage\*1
- Comprehensive warranty & service packages up to 5 years
- Advanced calibration, print layout and job costing functionality
- 24" & 44" models with optional SpectroProofer, Auto-Take-Up & HDD

Learn more,  
visit [www.epson.com.au/prographics](http://www.epson.com.au/prographics)



# Epson SureColor Photo Range

## SC-P7070 / SC-P9070

### Product Specifications

PRINT SPECIFICATIONS		ENVIRONMENTAL	
Printhead	PrecisionCore®	Operational Temperature	10° to 35° C (15-25° C recommended) 10 - 35° C
Print Modes	Uni & Bi-directional	Operational Humidity	20 to 80% with no condensation (40-60% recommended)
Print Technology	VSDT, auto head alignment, auto nozzle checking, auto cleaning, barcode print system, auto Pk & Mk switching	Power Supply	100 - 240 V, 50 Hz - 60 Hz AC, 2A
Nozzle Configuration	360 per colour, 10 active channels	Power Consumption	SC-P6070: 65W Operating / Standby 19W / 2W Sleep SC-P8070: 75W Operating / Standby 19W / 2W Sleep
Max Resolution	2,880 × 1,440dpi	Operating Noise	47dB
Min Droplet Size	3.5pl	PHYSICAL	
Ink Family	Epson UltraChrome® HDX	Dimensions (WxHxD)	Paper Basket Closed: SC-P7070: 1,356 x 1,218 x 667mm. SC-P9070: 1,864 x 1,218 x 667mm. Paper Basket Open: SC-P7070: 1,356 x 1,218 x 903mm. SC-P9070: 1,864 x 1,218 x 1,318mm
Ink Type	Aqueous all-pigment	Weight (without ink)	SC-P7070: 101kg. SC-P9070: 135kg
Ink Colours	Matte Black, Photo Black, Light Black, Cyan, Light Cyan, Vivid Magenta, Vivid Light, Magenta, Yellow, Light Light Black OR Violet*1	WHAT'S IN THE BOX	
Ink cartridge size	150ml/350ml/700ml	Printer, Stand, Power Cord, Set of 110ml Inks (note 20-50% may be used during initialisation), 1 x Roll Media Adaptor Set, 1 x Maintenance Tanks, Installation / Safety manual, Utility software & User manual (CD), SC-P9070 2 x Maint Tanks	
PERFORMANCE*2		INK AND CONSUMABLES	
Draft Mode	360 x 360dpi, 0.8 minutes	C13T770 Series	UltraChrome HDX 150ml C,PK,MK,VM,Y,O,G,LC,VLM,LK,LLK/V
Normal Mode	360 x 720dpi, 1.5 minutes	C13T769 Series	UltraChrome HDX 350ml C,PK,MK,VM,Y,O,G,LC,VLM,LK,LLK/V
Fine Mode	720x x720dpi, 3.3 minutes	C13T768 Series	UltraChrome HDX 700ml C,PK,MK,VM,Y,O,G,LC,VLM,LK,LLK/V
Super Fine Mode	720 x 1440dpi, 8.1 minutes	C13T699700	Maintenance Tank
Super Photo Mode	2880 x 1440dpi, 13.4 minutes	CONFIG BUILDS	
MEDIA SUPPORT		SCP70701YR	SC-P7070
Format	Roll and cut sheet	SCP7070SP1YR	SC-P7070 + SpectroProofer ILS30
Size	SC-P7070: 254-610mm wide x 150mm diameter 3" core / 103mm diameter 2" core roll, A4-A1+ sheet. SC-P9070: 254-1118mm wide x 150mm diameter 3" core / 103mm diameter 2" core roll, A4-B0+ sheet	SCP70703YR	SC-P7070 + CoverPlus 2Yr Service
Thickness	0.08-0.5mm roll / 0.08-1.5mm sheet	SCP7070SP3YR	SC-P7070 + SpectroProofer + CoverPlus 2Yr Service
Min Margins	0mm top, left, right & bottom roll 3mm top, 0mm left & right, 14mm bottom sheet	SCP70705YR	SC-P7070 + CoverPlus 2 x 2Yr Service
Loading	Front spindle-less single roll / top single sheet	SCP7070SP5YR	SC-P7070 + SpectroProofer + CoverPlus 2 x 2Yr Service
Handling	Auto and manual tension control, high-speed heavy-duty rotary auto-cutter (under 4s per page) & Media Barcode System	SCP90701YR	SC-P9070
Output	Integrated folding bin Optional Auto Take Up (SC-P9070 only)	SCP9070SP1YR	SC-P9070 + SpectroProofer ILS30
OPERATION		SCP90703YR	SC-P9070 + CoverPlus 2Yr Service
Control Panel	2.7" Colour LCD	SCP9070SP3YR	SC-P9070 + SpectroProofer + CoverPlus 2Yr Service
Interface	High Speed USB 2.0 Ethernet 10Base-T / 100Base-TX / 1000 Base-T	SCP90705YR	SC-P9070 + CoverPlus 2 x 2Yr Service
HDD	320GB (Optional)	SCP9070SP5YR	SC-P9070 + SpectroProofer + CoverPlus 2 x 2Yr Service
Memory	1GB Main + 64MB Network	OPTIONS	
Included Software	CD: Printer Driver, LFP RemotePanel 2, EpsonNet Setup, EpsonNet Config, EpsonNet Print (Windows only), Epson Color Calibration Utility Web Downloadable: LFP Accounting Tool, Epson Print Layout, HDD Utility Software, LFP print plug-in for Office	C12C815321	Optional 44" Auto take-Up
OS Compatibility	Mac OS X 10. 6.8 or later, Windows 10, Windows 8/8.1, Win 7, Win 7 x64, Win Vista, Win Vista x64 & Win XP	C12C811241	Additional Roll Media Adapter Set
Software Compatibility	Compatible with a wide range of design, production, workflow management and RIP software	C12C890121	Optional Roll Paper Belt
		C12C815331	Replacement Auto Cutter Blade
		C12C848031	Optional 320GB HDD (SC-P8070 only)
		SPECTR024SP	24" Spectro Kit
		SPECTR044SP	44" Spectro Kit
		COVERPLUS*3	
		1YWSCP7070	CoverPlus 1Yr Service Pack SC-P7070
		2YWSCP7070	CoverPlus 2Yr Service Pack SC-P7070
		1YWSCP9070	CoverPlus 1Yr Service Pack SC-P9070
		2YWSCP9070	CoverPlus 2Yr Service Pack SC-P9070

- \*1 At time of installation the end user needs to choose to configure the machine with either Light Light Black or Violet ink. Once this choice has been made it is final and cannot be undone or switched at a later time. 99% Pantone requires configuration with Violet Ink. Configured with Light Light Black provides 98% pantone coverage.
- \*2 Figures represent print times only for the Epson test sample image as shown, produced on Plain (draft – fine modes) and Premium Photo paper (super fine & super photo modes). Print speeds are engine only with total throughput time dependant on workflow configuration, paper type, software, file format / size, print resolution, ink coverage, networking, and other factors.
- \*3 Service Packs enable basic warranty cover to be extended. One or more Service Packs can be ordered in conjunction with the various printer configurations &/or options to enable cover for 1, 2, 3, 4 and 5 year periods (total cover cannot exceed 5 years). Service and support is only provided for product supplied through Epson Australia. This facility is provided in conjunction with the Authorised Large Format Reseller through which the product is ordered. Limitations apply to the provision of warranty upgrades and on-site service. Regional locations and certain installation situations may attract additional charges. Service may be restricted or limited when equipment is used outside of specification &/or with non-Epson consumables. For full details on coverage, terms and limitations please review the warranty terms listed on this web-site and contact Epson Australia or one of our Authorised Large Format Resellers if you have questions or concerns.

### Better Products for a Better Future

Epson is the registered trademark of Seiko Epson Corporation. All other names and company names used herein are for identification purpose only and may be the trademarks or registered trademarks of their respective owners. Epson disclaims any and all rights in those marks. All print samples shown herein are simulations. Specifications are subject to change without notice.

V1.0 September 2015

Epson CoverPlus

Fast. Reliable. Professional

**EPSON**  
EXCEED YOUR VISION

**FUJIFILM**

For more information or detailed product specification, please call or visit us at

**FUJIFILM Business Innovation Australia Pty Ltd**

8 Khartoum Road MACQUARIE PARK NSW 2113 Australia | Tel. +61 2 9856 5000 | [fujifilm.com/fbau](http://fujifilm.com/fbau)

FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation.  
V1.0 April 2021