



CAD/AEC/GIS • POS • MAPPING • EDUCATION

Epson SureColor T3465 (24")/T5465 (36")

- Designed for CAD, GIS, POS, posters and educational applications
- Prints on cut-sheet and roll media
- Produces an A1 print in as little as 22 seconds
- Economical operation with low power consumption and cost-effective ink cartridges in a choice of up to 700 ml capacity
- Features Epson's latest PrecisionCore® print head technology
- Uses all-pigment Ultrachrome™ XD2 ink for scratch and moisture resistant prints with super fine lines and solid fills
- Optional Epson scanner and BIJ printer support for copy, scan and enlargement functionality*¹
- Comprehensive warranty with on-site service cover extendable up to 5 years (includes print head)*²

Epson SureColor Technical Range SCT3465/5465

Product Specifications

Print Specifications		UltraChrome™ XD2 Aqueous Pigment Inks	
Printhead	PrecisionCore™ TFP	110 ml Cartridges	
Printing Resolution	2,400 x 1,200 dpi maximum	UltraChrome™ XD2 Black	C13T41V500
Ink Type	UltraChrome XD2 aqueous pigment ink	UltraChrome™ XD2 Cyan	C13T41V200
Colours	Magenta, Yellow, Cyan, Black	UltraChrome™ XD2 Magenta	C13T41V300
Ink Cartridge Sizes	110 ml/ 350 ml/ 700 ml (supports mixed size cartridges)	UltraChrome™ XD2 Yellow	C13T41V400
Maximum Printing Speed	25 secs (24")/A1 on plain paper 22 secs (36")/A1 on plain paper 36 secs (36")/A0 on plain paper	350 ml Cartridges	
Nozzle Configuration	800 nozzles per colour	UltraChrome™ XD2 Black	C13T41M500
Variable Drop Size	Yes, 4.0 pl minimum	UltraChrome™ XD2 Cyan	C13T41M200
Paper Handling		UltraChrome™ XD2 Magenta	C13T41M300
Paper Loading	Cut-sheet and rolls load from the front	UltraChrome™ XD2 Yellow	C13T41M400
Media Width	Roll: 329 mm to 610 mm (24"), 914 mm (36") max roll weight 12 kg 2/3" core ³ , max 150/170 mm diameter Single sheet: 210 mm to 610 mm (24"), 914 mm (36")	700 ml Cartridges	
Paper Thickness	Up to 0.3 mm	UltraChrome™ XD2 Black	C13T41L500
Connectivity	USB 3.0, 1000/100/10 base-T network, WiFi, WiFi direct, AirPrint	UltraChrome™ XD2 Cyan	C13T41L200
RAM	1 GB physical memory	UltraChrome™ XD2 Magenta	C13T41L300
Emulations	HPGL/2, HP-RTL ⁴	UltraChrome™ XD2 Yellow	C13T41L400
OS Compatibility	Windows 10/8.1/8/7/Vista/XP MacOS 10.6.8 or later	Consumables	
Product Features	Direct USB printing ⁵ Optional Epson Scanner and BJJ printer enlarge/copy support ^{*1}	Maintenance Box	C13T699700
Software Utilities	LFP Print Plug-In for MS-Office LFP Accounting Tool Epson Edge Dashboard	Auto Cutter Blade	C13S902007
Dimensions (W x D x H)		Borderless Pad Kit	C13S400064
Floor-Standing Model	T3465 – 1,080 mm x 750 mm x 1,070 mm T5465 – 1,385 mm x 750 mm x 1,070 mm	Options	
Power Rating	Energy Star compliant	Roll Feed Spindle 24"	C12C933281
Energy Usage		Roll Feed Spindle 36"	C12C933301
Operating	34 W	Ordering Configurations	
Standby	13 W	<i>All configurations supplied with 110 ml ink cartridges</i>	
Sleep	1.3 W	1 Year On-site Warranty	
Acoustic Noise Level	Approx. 50 dB(A)	T3465 Printer inc stand + basket	SCT34651YR
		T5465 Printer inc stand + basket	SCT54651YR
		3 Year On-site Service Cover	
		T3465 Printer inc stand + basket	SCT34653YR
		T5465 Printer inc stand + basket	SCT54653YR
		5 Year On-site Service Cover	
		T3465 Printer inc stand + basket	SCT34655YR
		T5465 Printer inc stand + basket	SCT54655YR
		What's in the box	
		Printer, printer stand and basket, a set of 110 ml ink cartridges, AC power cable, setup guide, software CD, maintenance box	

^{*1} Supports selected Epson scanners. Please visit the relevant Epson website.

^{*2} Additional charges may apply for on-site service in non-metro areas and warranty cover may be limited if equipment is not operated and maintained appropriately. For terms and conditions on Epson Australia and New Zealand service and warranty cover please refer to the relevant web sites.

^{*3} 3" core for plain paper rolls only.

^{*4} HP-GL/2 and HP RTL are trademarks of Hewlett-Packard Company. Printer may not print HP-GL/2 or HP RTL language data accurately depending on your system environment or type of print data use. In order to ensure correct printing results, please make sure that you run a printing test prior to deciding on purchasing the printer. Ask your local Epson representative or Epson authorised reseller for your test.

^{*5} For details please visit the relevant Epson websites

For further information please contact Epson Australia Pty Limited ABN 91 002 625 783 or visit www.epson.com.au. Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners. Product information is subject to change without prior notice.



Better Products for a Better Future

To find out more visit www.epson.com.au/technical

Epson Australia Pty Ltd
Level 1, 3 Talavera Road
Macquarie Park NSW 2113
Tel: 02 8899 3666
www.epson.com.au

Epson New Zealand
Level 2, 9 Fanshawe Street
Auckland 1010
Tel: 09 366 6855
www.epson.co.nz

Epson CoverPlus
Fast. Reliable. Professional



PRECISIONCORE



YOUR EPSON RESELLER

FUJIFILM

For more information or detailed product specification, please call or visit us at
FUJIFILM Business Innovation Australia Pty Ltd

FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation.

V1.0 April 2021

8 Khartoum Road MACQUARIE PARK NSW 2113 Australia
Tel. +61 2 9856 5000 | fujifilm.com/fbau